



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

6112 42nd Street  
79407-0000, TX Lubbock  
Phone: 806-698-6329  
Fax: 806-698-6805



## BAB2050 BAB2050 BRKR A

*Eaton Corp*

Catalog Number	BAB2050
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, Bolt-On Mounting, High Intensity Discharge, 50 A, 10 Kaic, Two-Pole, 120/240 V, Non-Interchangeable, Q7, Bab
Weight per unit	0.6500 (lbs/each)
Product Category	2 Pole Standard Trip Bolt-On

### Features

dimensions	3.8000 IN X 2.2000 IN X 4.8000 IN
interrupt rating	10
Poles	2
Voltage Rating	120/240 V

### Descriptions

Description	BAB2050 BRKR A
extra long description	ETN BAB2050 BAB2050 BRKR A
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,Bolt-on mounting, High intensity discharge,50 A,10 kAIC,Two-pole,120/240 V,Non-Interchangeable,Q7,BAB
Product Type	BAB2050 BRKR A
Special Features	Bolt-on mounting

### Manufacturer Information

Brand	Eaton
GTIN	00786679302507
Manufacturers Part Number	BAB2050
UPC	786679302507

### Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

### Availability

Status	Inactive
--------	----------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

6112 42nd Street  
79407-0000, TX Lubbock  
Phone: 806-698-6329  
Fax: 806-698-6805

## Packaging

Carton	1
Package	12
Weight Per each	0.65

## Uses, Certifications, and Standards

Application	OtherGeneration - Renewable Energy - Alternative EnergyGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - OtherResidential Bldgs & Facilities - Residential Bldgs & Facilities - Other
standard	CSA Certified,UL Listed