

Eaton BAB2070

Catalog Number: BAB2070

Eaton BAB thermal magnetic circuit breaker, Quicklag industrial thermal-magnetic circuit breaker, Bolt-on mounting, 70 A, 3 kAIC, Two-pole, 240/415 V, Non-Interchangeable, Q7, BAB

General specifications

Product Name	Catalog Number
Eaton BAB thermal magnetic circuit breaker	BAB2070
	UPC
	786679302705
Product Length/Depth	Product Height
3.6 in	3.7 in
Product Width	Product Weight
2.2 in	1.5 lb
Warranty	Certifications
1 year	CSA Certified
	UL Listed
Catalog Notes	
HACR rated	



Physical Attributes

Circuit breaker type

BAB

Mounting Method

Bolt-on

Number of poles

Two-pole

Type

Quicklag industrial thermal-magnetic circuit breaker

Performance Ratings

Amperage Rating

70 A

Interrupt rating

10 kAIC

Trip Type

Non-Interchangeable

Voltage rating

120/240 V

Miscellaneous

Quantity

7

Special features

Bolt-on mounting

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Multimedia

[Circuit Breakers Explained](#)

Specifications and datasheets

[Eaton Specification Sheet - BAB2070](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)