

Eaton BAB3015C

Catalog Number: BAB3015C

Eaton BAB thermal magnetic circuit breaker, Quicklag industrial thermal-magnetic circuit breaker, Bolt-on mounting, 15 A, 3 kAIC, Three-pole, 240/415 V, Non-Interchangeable, Q32, BAB

General specifications



Product Name	Catalog Number
Eaton BAB thermal magnetic circuit breaker	BAB3015C
	UPC
	786679304327
Product Length/Depth	Product Height
3.8 in	4.9 in
Product Width	Product Weight
3.2 in	0.85 lb
Warranty	Certifications
1 year	UL Listed
	CSA Certified
Catalog Notes	
HACR rated	

Physical Attributes

Circuit breaker type

BAB

Mounting Method

Bolt-on

Number of poles

Three-pole

Type

Quicklag industrial thermal-magnetic circuit breaker

Performance Ratings

Amperage Rating

15 A

Interrupt rating

10 kAIC

Trip Type

Non-Interchangeable

Voltage rating

120/240 V

Miscellaneous

Quantity

32

Special features

Switching neutral

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Multimedia

[Circuit Breakers Explained](#)

Specifications and datasheets

[Eaton Specification Sheet - BAB3015C](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)