

Eaton BAB thermal magnetic circuit breaker

BAB3015H

UPC:786679303153

Dimensions:

- **Height:** 4.9 IN
- **Length:** 3.8 IN
- **Width:** 3.2 IN

Weight:1 LB

Notes:HACR rated

Warranties: No Data

Specifications:

- **Type:** Quicklag industrial thermal-magnetic circuit breaker
- **Special Features:** Bolt-on mounting
- **Amperage Rating:** 15A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 240V
- **Trip Type:** Non-Interchangeable
- **Circuit Breaker Type:** BAB

Supporting documents:

- [Loadcenters and Circuit Breakers](#)
- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - BAB3015H](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data



Eaton BAB thermal magnetic circuit breaker

BAB3015H

UPC:786679303153

Dimensions:

- **Height:** 4.9 IN
- **Length:** 3.8 IN
- **Width:** 3.2 IN

Weight:1 LB

Notes:HACR rated

Warranties: No Data

Specifications:

- **Type:** Quicklag industrial thermal-magnetic circuit breaker
- **Special Features:** Bolt-on mounting
- **Amperage Rating:** 15A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 240V
- **Trip Type:** Non-Interchangeable
- **Circuit Breaker Type:** BAB

Supporting documents:

- [Loadcenters and Circuit Breakers](#)
- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - BAB3015H](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data

