

Eaton BAB3020H

Catalog Number: BAB3020H

Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, 20A, BAB type, 10 kAIC, Bolt-on mounting, Three-pole, Non-Interchangeable, 240V



General specifications

Product Name	Catalog Number
Eaton BAB thermal magnetic circuit breaker	BAB3020H
	UPC
	786679303207
Product Length/Depth	Product Height
3.375 in	3.5 in
Product Width	Product Weight
3 in	0.9 lb
Certifications	Catalog Notes
UL Listed	HACR rated
CSA Certified	



Powering Business Worldwide

Physical Attributes

Circuit breaker type

BAB

Number of poles

Three-pole

Type

Quicklag industrial thermal-magnetic circuit breaker

Performance Ratings

Amperage Rating

20 A

Interrupt rating

10 kAIC

Trip Type

Non-Interchangeable

Voltage rating

240 V - 240 V

Miscellaneous

Special features

Bolt-on mounting

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Multimedia

[Circuit Breakers Explained](#)

Specifications and datasheets

[Eaton Specification Sheet - BAB3020H](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)