# Eaton BAB3025H

# Catalog Number: BAB3025H

Eaton BAB thermal magnetic circuit breaker, Quicklag Industrial, 25A, 10 kAIC, Bolt-on mounting, Three-pole, Non-Interchangeable, 240V

# General specifications



Product Name Catalog Number

Eaton BAB thermal magnetic circuit BAB3025H

breaker

786679303252

**UPC** 

Product Length/Depth Product Height

3.5 in 3 in

Product Width Product Weight

3.2 in 0.9 lb

Certifications Catalog Notes
UL Listed HACR rated

CSA Certified



# **Physical Attributes**

Circuit breaker type

BAB

Number of poles

Three-pole

Type

Quicklag industrial thermal-magnetic circuit breaker

## Performance Ratings

Amperage Rating

25 A

Interrupt rating

10 kAIC

Trip Type

Non-Interchangeable

Voltage rating

240 V - 240 V

## Miscellaneous

#### Special features

Bolt-on mounting

#### Resources

#### **Brochures**

Loadcenters and Circuit Breakers

#### Catalogs

Eaton's Volume 4—Circuit Protection

Multimedia

Circuit Breakers Explained

Specifications and datasheets

Eaton Specification Sheet - BAB3025H



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia