

Eaton BAB3035H

Catalog Number: BAB3035H

Eaton BAB thermal magnetic circuit breaker, Quicklag industrial thermal-magnetic circuit breaker, 35 A, 10 kAIC, Three-pole, 240 V, Non-interchangeable, BAB,120-240 V Shunt trip

General specifications



| | |
|--|-----------------------|
| Product Name | Catalog Number |
| Eaton BAB thermal magnetic circuit breaker | BAB3035H |
| | UPC |
| | 786679303351 |
| Product Length/Depth | Product Height |
| 3.375 in | 3.25 in |
| Product Width | Product Weight |
| 3 in | 0.95 lb |
| Warranty | Certifications |
| 1 year | UL Listed |
| | CSA Certified |
| Catalog Notes | |
| HACR rated | |

Physical Attributes

Circuit breaker type

BAB

Number of poles

Three-pole

Type

Quicklag industrial thermal-magnetic circuit breaker

Performance Ratings

Amperage Rating

35 A

Interrupt rating

10 kAIC

Trip Type

Non-Interchangeable

Voltage rating

240 V - 240 V

Miscellaneous

Shunt trip

120-240V

Special features

Bolt-on mounting

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - BAB3035H](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)