

## Eaton BAB thermal magnetic circuit breaker

**BAB3045H**

**UPC:**786679303450

**Dimensions:**

- **Height:** 4.7 IN
- **Length:** 3.8 IN
- **Width:** 3.2 IN

**Weight:**.95 LB

**Notes:**HACR rated

**Warranties:**

- 1 year

**Specifications:**

- **Type:** Quicklag industrial thermal-magnetic circuit breaker
- **Special Features:** Bolt-on mounting
- **Amperage Rating:** 45A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 240V
- **Trip Type:** Non-Interchangeable
- **Quantity:** Q32
- **Circuit Breaker Type:** BAB

**Supporting documents:**

- [Loadcenters and Circuit Breakers](#)
- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - BAB3045H](#)

**Certifications:**

- UL Listed
- CSA Certified

**Product compliance:** No Data





## Eaton BAB thermal magnetic circuit breaker

**BAB3045H**

**UPC:**786679303450

**Dimensions:**

- **Height:** 4.7 IN
- **Length:** 3.8 IN
- **Width:** 3.2 IN

**Weight:**.95 LB

**Notes:**HACR rated

**Warranties:**

- 1 year

**Specifications:**

- **Type:** Quicklag industrial thermal-magnetic circuit breaker
- **Special Features:** Bolt-on mounting
- **Amperage Rating:** 45A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 240V
- **Trip Type:** Non-Interchangeable
- **Quantity:** Q32
- **Circuit Breaker Type:** BAB

**Supporting documents:**

- [Loadcenters and Circuit Breakers](#)
- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - BAB3045H](#)

**Certifications:**

- UL Listed
- CSA Certified

**Product compliance:** No Data



