Eaton BAB3050H

Catalog Number: BAB3050H

Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,50 A,10 kAIC,Three-pole,240 V,Interchangeable,BAB,Distribution panels 240V (Three-phase, four-wire maximum),Four-wire,Three-phase

General specifications



Product Name

Eaton BAB thermal magnetic circuit

breaker

Product Length/Depth

3.8 in

Product Width

3.2 in

Warranty

1 year

Catalog Notes

HACR rated

Catalog Number

BAB3050H

UPC

786679303504

Product Height

4.9 in

Product Weight

1 lb

Certifications

UL Listed
CSA Certified





Physical Attributes

Circuit breaker type

BAB

Number of poles

Three-pole

Number of wires

4

Type

Quicklag industrial thermal-magnetic circuit breaker

Performance Ratings

Amperage Rating

50 A

Interrupt rating

10 kAIC

Trip Type

Non-Interchangeable

Voltage rating

240 V - 240 V

Miscellaneous

Special features

Bolt-on mounting

Used with

Distribution panels 240 V (Three-phase, four-wire maximum)

Resources

Brochures

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 4—Circuit Protection

Multimedia

Circuit Breakers Explained

Specifications and datasheets

Eaton Specification Sheet - BAB3050H



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia