# Eaton BAB3070H

## Catalog Number: BAB3070H

Eaton BAB thermal magnetic circuit breaker, Quicklag industrial thermal-magnetic circuit breaker, 70 A, 10 kAIC, Three-pole, 240 V, Interchangeable, BAB, Distribution panels 240V (Three-phase, four-wire maximum), Four-wire, Three-phase



## General specifications

#### **Product Name**

Eaton BAB thermal magnetic circuit

breaker

#### Product Length/Depth

3.9 in

**Product Width** 

3.2 in

Warranty

1 year

Catalog Notes

**HACR** rated

## Catalog Number

BAB3070H

UPC

786679303702

**Product Height** 

4.9 in

**Product Weight** 

1.05 lb

Certifications

UL Listed
CSA Certified



## Physical Attributes

Circuit breaker type

BAB

Mounting Method

Bolt-on

Number of poles

Three-pole

Number of wires

4

Type

Quicklag industrial thermal-magnetic circuit breaker

## Performance Ratings

Amperage Rating

70 A

Interrupt rating

10 kAIC

Trip Type

Non-Interchangeable

Voltage rating

240 V - 240 V

## Miscellaneous

Quantity

32

Special features

**Bolt-on mounting** 

Used with

Distribution panels 240 V (Three-phase, four-wire maximum)

## Resources

## Brochures

Loadcenters and Circuit Breakers

## Catalogs

Eaton's Volume 4—Circuit Protection

Multimedia

Circuit Breakers Explained

## Specifications and datasheets

Eaton Specification Sheet - BAB3070H



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia