

# Eaton BAF-3

Catalog Number: BAF-3

Eaton Bussmann series BAF fuse, Fast acting, 3 A, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 125 Vac|100 AIC at 250 Vac, Nickel-plated brass endcaps, Standard, 250 V

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Bussmann series BAF fuse	BAF-3
<b>UPC</b>	<b>Product Length/Depth</b>
051712320030	1.5 in
<b>Product Height</b>	<b>Product Width</b>
0.41 in	0.41 in
<b>Product Weight</b>	<b>Warranty</b>
0.25 lb	Not Applicable
<b>Compliances</b>	
CE Marked	

## Electrical rating

### Amperage Rating

3 A

### Interrupt rating

100 AIC at 250 Vac

10 kAIC at 125 Vac

### Voltage rating

250 V

## Physical details

### Material

Nickel-plated brass endcaps

### Packaging type

Standard

## General information

### Connection

Ferrule end x ferrule end

### Fuse indicator

Non-indicating

### Special features

Silver-plated fuse caps

## Resources

### Catalogs

[Bussmann series complete full line catalog no. 1007](#)

### Multimedia

[Bussmann series Fuseology](#)

### Specifications and datasheets

[Eaton Specification Sheet - BAF-3](#)

### Technical data sheets

[BAF-3~BUSS MIDGET FUSE](#)

### Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)