



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1612 E. Booth Road
72143-0000, AR Searcy
Phone: 501-368-0309
Fax: 501-368-0619



BC2SS10C0 8.5" 50LB #10SCREW BLK Nylon Barb CBL Tie *Panduit Corporation*

Catalog Number	BC2SS10C0
Manufacturer	Panduit Corporation
Description	Dome-Top® Barb Ty Clamp Tie, Standard Cross Section, #10 (M5) Screw, 8.5 (216MM) Length, Weather Resistant Nylon 6.6, Black, Standard Package.
Weight per unit	0.4190 (lbs/each)
Product Category	Cable Ties & Wraps

Features

media	Yes
Tensile Strength	50

Dimensions and Weight

Length	8.5
Width	NA

Descriptions

Description	8.5" 50LB #10SCREW BLK NYLON BARB CBL TIE
extra long description	PAN BC2S-S10-C0 Dome-Top® BC2S-S10-
Long Description	Dome-Top® barb ty clamp tie, standard cross section, #10 (M5) screw, 8.5 (216mm) length, weather resistant nylon 6.6, black, standard package.
Product Type	Dome-Top® BC2S-S10-C0 Locking Clamp Barb Tie, Black, Uv PA6.
Special Features	OUTDOOR

Manufacturer Information

Brand	Panduit®
GTIN	00074983523153
Manufacturers Part Number	BC2S-S10-C0
UPC	074983523153

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Tie

Packaging

Carton	100
Package	1000
Weight Per each	0.419

Uses, Certifications, and Standards

Application	General
standard	UL 62275 Compliant (Type 1, 11)