

Eaton BCH64

Catalog Number: BCH64

Eaton B-Line series datacomm and low voltage support fasteners, Capacity up to 300 4-Pair UTP 25 cat 5e or 2-strand Fiber Optic Cable or 185 CAT6 or 98 CAT6A, Cable hook, Wall mount, 1-4" J-hook, Pre-galvanized, Load capacity 30 lbs, Steel

General specifications



Product Name	Catalog Number
Eaton B-Line series single cable hook	BCH64
UPC	Product Length/Depth
781011047214	4.112 in
Product Height	Product Width
6.866 in	2 in
Product Weight	Certifications
0.56 lb	UL/CUL listed

Model

Type

Cable hook

Special features

Wall mount

Specifications

Load capacity

30 lb

Hook size

4 in

Number of J-hooks

1

Material/Finish

Material

Steel

Finish

Pre-galvanized

Resources

Brochures

[J-Hook color ID clip flyer](#)

Catalogs

[Communications and low voltage section fastener catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - BCH64](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)