

# Eaton BD1515

Catalog Number: BD1515

Eaton BR thermal magnetic circuit breaker, Type BD 1-Inch CTL plug-on circuit breaker, Includes rejection tab feature, 15-15 A, 10 kAIC, Single-pole, 120V, BD, #14-4 AWG Cu/Al, BD, Type BR Loadcenters



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR thermal magnetic circuit breaker	BD1515
	<b>UPC</b>
	786676369053

<b>Product Length/Depth</b>	<b>Product Height</b>
2.9 in	2.5 in

<b>Product Width</b>	<b>Product Weight</b>
1 in	0.35 lb

<b>Compliances</b>	<b>Certifications</b>
Federal Specifications Classification W-C375	UL 489

### Catalog Notes

All Type BD Duplex and BQ Quadplex circuit breakers carry listing for HACR applications. All 15 and 20 ampere single poles are switch duty rated.

## defaultTaxonomyAttributeLabel

### Type

Type BD 1-Inch CTL plug-on circuit breaker

### Special features

Includes rejection tab feature

### Amperage Rating

(2) 15A

### Voltage rating

120 V

### Circuit breaker type

BR

### Used with

Type BR Loadcenters

### Mounting Method

Plug-on

### Interrupt rating

10 kAIC

### Main circuit breaker

BD

### Wire size

#14-4 AWG Cu/Al

### Number of poles

Single-pole

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Specifications and datasheets

[Eaton Specification Sheet - BD1515](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)