


# Beams




- Quickly attaches conduit to beams.
- Fasteners will rotate 360°.
- Simply installed with a hammer.

## Push-Type Conduit To Beam Fasteners



UPC/Part Number	Catalog Number	Conduit Size	Flange Thickness	Box Qty.
781011 19310	<b>BP-8-U-2-4</b>	1/2" EMT	1/8" - 1/4"	100
781011 19315	<b>BP-8-U-5-8</b>	1/2" EMT	5/16" - 1/2"	100
781011 19320	<b>BP-8-U-9-12</b>	1/2" EMT	9/16" - 3/4"	100
781011 19405	<b>BP-12-U-2-4</b>	3/4" EMT 1/2" IMC, Rigid	1/8" - 1/4"	100
781011 19410	<b>BP-12-U-5-8</b>	3/4" EMT 1/2" IMC, Rigid	5/16" - 1/2"	100
781011 19415	<b>BP-12-U-9-12</b>	3/4" EMT 1/2" IMC, Rigid	9/16" - 3/4"	100
781011 19490	<b>BP-16-U-2-4</b>	1" EMT 3/4" IMC, Rigid	1/8" - 1/4"	100
781011 19495	<b>BP-16-U-5-8</b>	1" EMT 3/4" IMC, Rigid	5/16" - 1/2"	100
781011 19500	<b>BP-16-U-9-12</b>	1" EMT 3/4" IMC, Rigid	9/16" - 3/4"	100


**Ultimate  
Static Load  
Capacity**



25 Lbs.

Read safety/installation instruction sheets in packages before use. These products are designed for positioning only. No load rating.

- Unique **Guide-Rite** Fastener provides for fast and easy installation.
- Fasteners will rotate 360°.
- Simply installed with a hammer and pliers.



## Guide-Rite™ Conduit To Beam Fasteners




UPC/Part Number	Catalog Number	Conduit Size	Flange Thickness	Box Qty.
781011 18450	<b>BG-6-U-2-4*</b>	3/8"	1/8" - 1/4"	100
781011 18455	<b>BG-6-U-5-8*</b>	3/8"	5/16" - 1/2"	100
781011 18460	<b>BG-6-U-9-12*</b>	3/8"	9/16" - 3/4"	100
781011 18525	<b>BG-8-12-U-2-4</b>	1/2", 3/4"	1/8" - 1/4"	100
781011 18530	<b>BG-8-12-U-5-8</b>	1/2", 3/4"	5/16" - 1/2"	100
781011 18535	<b>BG-8-12-U-9-12</b>	1/2", 3/4"	9/16" - 3/4"	100
781011 18625	<b>BG-16-U-2-4</b>	1"	1/8" - 1/4"	100
781011 18630	<b>BG-16-U-5-8</b>	1"	5/16" - 1/2"	100
781011 18635	<b>BG-16-U-9-12</b>	1"	9/16" - 3/4"	100
781011 18680	<b>BG-20-U-2-4</b>	1 1/4"	1/8" - 1/4"	100
781011 18685	<b>BG-20-U-5-8</b>	1 1/4"	5/16" - 1/2"	100
781011 18690	<b>BG-20-U-9-12</b>	1 1/4"	9/16" - 3/4"	100
781011 18720	<b>BG-24-U-2-4</b>	1 1/2"	1/8" - 1/4"	50
781011 18725	<b>BG-24-U-5-8</b>	1 1/2"	5/16" - 1/2"	50
781011 18730	<b>BG-24-U-9-12</b>	1 1/2"	9/16" - 3/4"	50
781011 18760	<b>BG-32-U-2-4</b>	2"	1/8" - 1/4"	50
781011 18765	<b>BG-32-U-5-8</b>	2"	5/16" - 1/2"	50
781011 18770	<b>BG-32-U-9-12</b>	2"	9/16" - 3/4"	50

Patent #4958792

- \* BG-6 will accept the following range  $\varnothing.420 - \varnothing.675$ :  
1 1/2 thru 10/4 MC/AC cable  
and 5/16 or 3/8 flexible conduit

**Static Load  
Capacity**



Read safety/installation instruction sheets in packages before use.