



BIBD2/03FX, Double Sided Flex Rated Three Conductor Clear Insulated Multi-Tap Connector

By Burndy
Catalog # BIBD2/03FX



Aluminum UNITAP, Double Sided Entry, #14-2/0 Class B & C, #14-#1 Class G,H,I,K, DLO, 3 PORT

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory
- Suitable for Code and Flex Conductor
- Color-coordinated conductor port caps display wire range and classes of conductor accepted
- Screw port caps show installation torque information for easy reference

Application

Tap connections and in-line splice/reductions are made quickly and easily with the UNITAP™ line of connectors

General

Connector Type	Multi Tap
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBD, Multi-Port
UPC	621945438781
UPC 12 Digit	6219454387811

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

Conductor Size 14-2/0 AWG
Conductor Type

- AL C Str-Size
- CU C Str-Size

Certifications And Compliance

Certification - CSA Approved Yes
Industry Standard(s) UL 486A-486B
Standards - Industry Standards Met UL 486A-486B
Standards - RoHS Compliance Status CM
UL Listed Yes

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalogs - UNITAP™ Products](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50046931](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-BIBD2/03FX-SPEC-EN | REV 5/2024