



BIBD43FX, Double Sided Flex Rated Three Conductor Clear Insulated Multi-Tap Connector

By Burndy
Catalog # [BIBD43FX](#)



Aluminum UNITAP, Double Sided Entry, #14-#4 Class B & C, #14-#6 Class G,H,I,K, DLO, 3 PORT

Application

Tap connections and in-line splice/reductions are made quickly and easily with the UNITAP™ line of connectors

General

Connector Type	Multi Tap
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Number Of Ports	3
Plated	Y
Plating Type	Tin
Sub Brand	UNITAP
Temperature Rating	-40° C to 135 °C
Trade Name	UNITAP™
Type	BIBD, Multi-Port
UPC	621945438712
UPC 12 Digit	6219454387122

Dimensions

Dimension - Length Overall inch	1.268 in
---------------------------------	----------

Electrical Ratings

Amperage Rating	85 A
Voltage - Maximum	600 V

Conductor Related

Conductor - AL Str Size Range	14 AWG-4 AWG
Conductor Size	14-4 AWG
Conductor Type	<ul style="list-style-type: none">AL C Str-SizeCU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - UNITAP™ Products](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50046931](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-BIBD43FX-SPEC-EN | REV 8/2023