



BIT350FX, Single Sided Flex Rated Two Conductor Clear Insulated Multi-Tap Connector

By Burndy
Catalog # BIT350FX



Aluminum UNITAP, Tap - Same Side Entry, #10-350 Class B & C, #10-250 Class G,H,I,K, DLO, 2 PORT

Application

Clear Insulated Multiple Tap Connectors

General

Color Code	Red
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Hex Key	5/16 in
Installation Torque Recommended in-lb	310 in-lb
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Number Of Ports	2
Plated	Y
Plating Type	Tin Plated Aluminum
Sub Brand	UNITAP
Temperature Rating	135 °C
Trade Name	UNITAP™
Type	BIT, UNITAP
UPC	621945440029
UPC 12 Digit	6219454400299

Dimensions

Dimension - Height inch	2.5 in
Dimension - L Length Overall mm	56 mm
Dimension - Length Overall inch	2.22 in
Dimension - Width inch	2.38 in
Dimension - Width mm	60.45 mm

Electrical Ratings

Operating Voltage	600 V
Voltage - Maximum	600 V

Conductor Related

Conductor - Copper DLO Size Range	10 - 250 Str
Conductor - Copper Flex G Size Range	10 - 250 Str
Conductor - Copper Flex H Size Range	10 - 250 Str
Conductor - Copper Flex I Size Range	10 - 250 Str
Conductor - Copper Flex K Size Range	10 - 250 Str
Conductor - Copper Str Size Range	10 AWG - 350 kcmil
Conductor Size	10 AWG-350 KCMIL
Conductor Type	<ul style="list-style-type: none">• AL C Str-Size• CU C Str-Size• CU C Flex-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - UNITAP™ Products](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50046931](#)



A proud member of the Hubbell Family.

