

# Eaton BJ2100

Catalog Number: BJ2100

Eaton Type BJ 1-inch Plug-on Main Breakers, 1-inch Plug-on main breaker, 100 A, 10 kAIC, Two-pole, 120/240 V, BJ, Common, Plug-on, #2 AWG-300 kcmil Cu/Al, BJ



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BJ sub feed main circuit breaker	BJ2100
<b>UPC</b>	<b>Product Length/Depth</b>
782116484294	6.5 in
<b>Product Height</b>	<b>Product Width</b>
2.5 in	3.5 in
<b>Product Weight</b>	<b>Warranty</b>
1.8 lb	Limited lifetime residential, 1 year commercial
<b>Compliances</b>	<b>Certifications</b>
Federal Specifications Classification W-C375	UL 489
	<b>Catalog Notes</b>
	Requires at least a 150 A Loadcenter, Breaker uses two 1-Inch (25.4mm) pole spaces and two 1-Inch (25.4mm) pole spaces on right side of loadcenter.

**Type**

1-inch Plug-on main breaker

**Amperage Rating**

100 A

**Voltage rating**

120/240 V

**Trip Type**

Common

**Circuit breaker frame type**

BJ

**Mounting Method**

Plug-on

**Interrupt rating**

10 kAIC

**Main circuit breaker**

BJ

**Connection**

Plug-on

**Wire size**

#2 AWG-300 kcmil Cu/Al

**Number of poles**

Two-pole

**Catalogs**

[Eaton's Volume 1—Residential and Light Commercial](#)

**Specifications and datasheets**

[Eaton Specification Sheet - BJ2100](#)