Eaton BJ2150

Catalog Number: BJ2150

Eaton Type BJ 1-inch Plug-on Main Breakers,1-inch Plug-on main breaker,150 A,10 kAIC,Two-pole,120/240 V,Common,Plug-on,#2 AWG-300 kcmil Cu/AI,BJ

General specifications

Product Name Catalog Number

Eaton BJ sub feed main circuit breaker BJ2150

UPC Product Length/Depth

786676367103 6.5 in

Product Height Product Width

2.5 in 3.5 in

Product Weight Warranty

1.8 lb Limited lifetime residential, 1 year

commercial

Compliances Certifications

Federal Specifications Classification W- UL 489

C375

Catalog Notes

Requires at least a 150 A Loadcenter, Breaker uses two 1-Inch (25.4mm) pole spaces and two 1-Inch (25.4mm) pole spaces on right side of loadcenter.





default Taxonomy Attribute Label

Type

1-inch Plug-on main breaker

Amperage Rating

150 A

Voltage rating

120/240 V

Trip Type

Common

Circuit breaker frame type

BJ

Mounting Method

Plug-on

Interrupt rating

10 kAIC

Main circuit breaker

BJ

Connection

Plug-on

Wire size

#2 AWG-300 kcmil Cu/AI

Number of poles

Two-pole

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Specifications and datasheets

Eaton Specification Sheet - BJ2150



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia