

Eaton BJ2225

Catalog Number: BJ2225

Eaton Type BJ 1-inch Plug-on Main Breakers, 1-inch Plug-on main breaker, 225 A, 10 kAIC, Two-pole, 120/240 V, Common, Plug-on, #2 AWG-300 kcmil Cu/Al, BJ



General specifications

Product Name	Catalog Number
Eaton BJ sub feed main circuit breaker	BJ2225
UPC	Product Length/Depth
786676367257	6.5 in
Product Height	Product Width
2.5 in	3.5 in
Product Weight	Warranty
1.8 lb	Limited lifetime residential, 1 year commercial
Compliances	Certifications
Federal Specifications Classification W-C375	UL 489
	Catalog Notes
	Requires at least a 150 A Loadcenter, Breaker uses two 1-Inch (25.4mm) pole spaces and two 1-Inch (25.4mm) pole spaces on right side of loadcenter.

Type

1-inch Plug-on main breaker

Amperage Rating

225 A

Voltage rating

120/240 V

Trip Type

Common

Circuit breaker frame type

BJ

Mounting Method

Plug-on

Interrupt rating

10 kAIC

Main circuit breaker

BJ

Connection

Plug-on

Wire size

#2 AWG-300 kcmil Cu/Al

Number of poles

Two-pole

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - BJ2225](#)