

Eaton BJ3125

Catalog Number: BJ3125

Eaton Type BJ 1-Inch Plug-on Main Breakers, Type BJ 1-Inch plug-on main breakers, 125 A, 10 kAIC, Three-pole, 240V, BJ, Common breaker trip, #2 AWG-300 kcmil Cu/Al, BJ



General specifications

Product Name

Eaton BR thermal magnetic circuit breaker

Catalog Number

BJ3125

UPC

786676368308

Product Length/Depth

8 in

Product Height

3.5 in

Product Width

3.5 in

Product Weight

2.5 lb

Warranty

Limited lifetime residential, 1 year commercial

Compliances

Federal Specifications Classification W-C375

Certifications

UL 489

Catalog Notes

Requires at least a 150 A Loadcenter. Breaker uses three 1-Inch (25.4mm) pole spaces on left side and three 1-Inch (25.4mm) pole spaces on right side of loadcenters.

defaultTaxonomyAttributeLabel

Type

Type BJ 1-Inch plug-on main breakers

Amperage Rating

125 A

Voltage rating

240 V - 240 V

Trip Type

Common breaker trip

Mounting Method

Plug-on

Interrupt rating

10 kAIC

Main circuit breaker

BJ

Wire size

#2 AWG-300 kcmil Cu/Al

Number of poles

Three-pole

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - BJ3125](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)