

# Specifications

## Eaton BJ94



Photo is representative

Eaton Crouse-Hinds series XJG bonding jumper, Rigid/IMC, 4" maximum conduit movement, Used with XJG94 HDG, 3-1/2" trade size

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series XJG bonding jumper
<b>CATALOG NUMBER</b>	BJ94
<b>UPC</b>	782274992006
<b>PRODUCT LENGTH/DEPTH</b>	30 in
<b>PRODUCT HEIGHT</b>	0.88 in
<b>PRODUCT WIDTH</b>	0.19 in
<b>PRODUCT WEIGHT</b>	3.2 lb



Powering Business Worldwide

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

## Product specifications

<b>CONDUIT TYPE</b>	Rigid/IMC
<b>TRADE SIZE</b>	3-1/2"
<b>CONDUIT MOVEMENT - MAX</b>	4"
<b>SPECIAL FEATURES</b>	Used with XJG94 HDG

## Resources

<b>BROCHURES</b>	<a href="#">Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure</a>
<b>CATALOGS</b>	<a href="#">Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification</a> <a href="#">XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - BJ94</a> <a href="#">Expansion and Deflection Couplings</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.

# Specifications

## Eaton BJ94



Photo is representative

Eaton Crouse-Hinds series XJG bonding jumper, Rigid/IMC, 4" maximum conduit movement, Used with XJG94 HDG, 3-1/2" trade size

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series XJG bonding jumper
<b>CATALOG NUMBER</b>	BJ94
<b>UPC</b>	782274992006
<b>PRODUCT LENGTH/DEPTH</b>	30 in
<b>PRODUCT HEIGHT</b>	0.88 in
<b>PRODUCT WIDTH</b>	0.19 in
<b>PRODUCT WEIGHT</b>	3.2 lb



Powering Business Worldwide

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

## Product specifications

<b>CONDUIT TYPE</b>	Rigid/IMC
<b>TRADE SIZE</b>	3-1/2"
<b>CONDUIT MOVEMENT - MAX</b>	4"
<b>SPECIAL FEATURES</b>	Used with XJG94 HDG

## Resources

<b>BROCHURES</b>	<a href="#">Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure</a>
<b>CATALOGS</b>	<a href="#">Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification</a> <a href="#">XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - BJ94</a> <a href="#">Expansion and Deflection Couplings</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

