

Eaton BKG2G125

Catalog Number: BKG2G125

Eaton Pow-R-Xpress Main Circuit Breaker Kit, PDG2XG CONVERTIBLE, 125A



General specifications

Product Name	Catalog Number
Eaton Pow-R-Xpress main breaker kit	BKG2G125
UPC	Product Length/Depth
786689362409	22 in
Product Height	Product Width
5 in	9 in
Product Weight	Compliances
16 lb	NEMA Compliant
Certifications	
UL 67	

Physical Attributes

Phase

Single-phase, three-phase

Type

CONV MCB KIT

Performance Ratings

Amperage Rating

125 A

Rated operational current

350A

Miscellaneous

Series

Pow-R-stock

Resources

Brochures

[Pow-R-Xpress stocking program flyer](#)

[Pow-R-Xpress quick selector reference guide](#)

[Eaton's Pow-R-Xpress stocking program](#)

Multimedia

[Pow-R-Line Xpert family overview](#)

Specifications and datasheets

[Eaton Specification Sheet - BKG2G125](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)