

# Eaton BKLGE600T

Catalog Number: BKLGE600T

MAIN BKR KIT 480V MAX 1 OR 3PH 600A LG TOP MOUNTING

## General specifications

Product Name	Catalog Number
Eaton Pow-R-Stock main breaker kit	BKLGE600T
UPC	Product Length/Depth
786687010753	5.5 in
Product Height	Product Width
12 in	5.5 in
Product Weight	Certifications
16 lb	UL Listed



## defaultTaxonomyAttributeLabel

### Type

Breaker Kit

### Bus material

Copper

### Bus Rating

600 A

### Circuit breaker type

LG

### Feed type

Top

### Mounting

Top

### Nominal frequency

50 Hz

### Number Of Poles

Three-pole

### Operating Temperature

40°C

### Phase

Single-phase, three-phase

### Short-circuit rating

35000 kA

### Wire size

#4 AWG-350 kcmil

### Application

Commercial construction

### Indicators

Local

### Number of conductors

1 per phase

### Operator

Manual

### Primary voltage

277Y/480 V

### Series

## Resources

### Multimedia

[Pow-R-Line Xpert family overview](#)

### Specifications and datasheets

[Eaton Specification Sheet - BKLGE600T](#)

C

Voltage - max

600



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)