

# Eaton BL125

Catalog Number: BL125

Eaton B-Line series strut mounting bracket, Conduit and cable, 1" Height, 1" Length, 1" Width, 0.314lbs, Conduit size: 1.25" EMT/Rigid, Conduit and cable clamps, 1.4" Max mount size, 1.725" Min, 200 lbs load capacity, Pre-galvanized



## General specifications

Product Name	Catalog Number
Eaton B-Line series conduit and cable clamp	BL125
	UPC
	799038601654
Product Length/Depth	Product Height
1 in	1 in
Product Width	Product Weight
1 in	0.314 lb
Certifications	
CE	
UL Listed	

## Application

### Application

Attaches to cable tray rungs and strut profiles

## Model

### Product Category

Conduit and cable

### Type

Conduit and cable clamps

## Specifications

### Size

Conduit size: 1.25 inch EMT/Rigid

### Load capacity

200 lbs

### Cable diameter - min

1.725 in

### Mounting dimensions - max

1.40

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - BL125](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)