



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1620 Highway 155
75803-8616, TX Palestine
Phone: 903-723-2141
Fax: 903-723-1451



BL200 SPRG 2" CNDT/CBL Clamp

Cooper B-Line/Cable Tray

Catalog Number	BL200
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Strut Mounting Bracket, Conduit and Cable, 1" Height, 1" Length, 1" Width, 0.406LBS, Conduit Size: 2" Emt/Rigid, Conduit and Cable Clamps, 1.98" Max Mount Size, 2.576" Min, 200 LBS Load Capacity, Pre-Galvanized
Weight per unit	0.4060 (lbs/each)
Product Category	Channel & Strut Fittings

Features

dimensions	1.0000 IN X 1.0000 IN X 1.0000 IN
------------	-----------------------------------

Material, Color, and Finish

Color	GLV
-------	-----

Descriptions

Description	SPRG 2" CNDT/CBL CLAMP
extra long description	B-LINE BL200 CONDUIT & CBL CLAMP, 2
Features	Eaton's B-Line series strut mounting brackets include a variety of strut clamps to help secure and support conduit and cables onto the channel
Long Description	Eaton B-Line series strut mounting bracket, Conduit and cable, 1" Height, 1" Length, 1" Width, 0.406lbs, Conduit size: 2" EMT/Rigid, Conduit and cable clamps, 1.98" Max mount size, 2.576" Min, 200 lbs load capacity, Pre-galvanized
Product Type	Conduit & CBL Clamp, 2" Emt & Rigid, G90

Manufacturer Information

Brand	Eaton
GTIN	00799038601685
Manufacturers Part Number	BL200
UPC	799038601685

Taxonomies, Classifications, and Categories

Category Description	BEAM, RA, EDGE, & PARALLEL CLAMPS
Type	Conduit and cable clamp

Packaging

Carton	1
Package	50
Weight Per each	0.406



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1620 Highway 155
75803-8616, TX Palestine
Phone: 903-723-2141
Fax: 903-723-1451

Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Commercial /
Institutional Buildings / Structures - OtherCommercial /
Institutional Buildings / Structures - Commercial/Inst Bldg
Structures - Aftermarket

standard

UL Listed,CE