



Туре

Catalog Number

Notes

# Contractor Select™ BLC Center Basket Troffer

## Available in 2' x 2' and 2' x 4' configurations

- Contractor Select<sup>™</sup> BLC options for the most popular and readily available configurations
- Slim 2-3/8" profile fits restrictive plenums and optimizes pallet space
- Dims to 10%
- Long-life LEDs deliver 80% lumen maintenance at 60,000 hours

Catalog Number	UPC	Description	Lumens	Input Watts	Voltage	Colot Temperature	Pallet qty.
BLC 2X2 3300LM 35K ADSM	193048323177	2x2 Center Basket Troffer, Curved, Smooth Diffuser	3329	30W	120-277	3500K	56
BLC 2X2 3300LM 40K ADSM	193048323269	2x2 Center Basket Troffer, Curved, Smooth Diffuser	3382	30W	120-277	4000K	56
BLC 2X4 4000LM 35K	191848536575	2x4 Center Basket Troffer, Square, Smooth Diffuser	4034	32W	120-277	3500K	28
BLC 2X4 4000LM 35K ADSM	193048323443	2x4 Center Basket Troffer, Curved, Smooth Diffuser	4034	32W	120-277	3500K	28
BLC 2X4 4000LM 40K	191848536629	2x4 Center Basket Troffer, Square, Smooth Diffuser	4098	32W	120-277	4000K	28
BLC 2X4 4000LM 40K ADSM	193048323511	2x4 Center Basket Troffer, Curved, Smooth Diffuser	4098	32W	120-277	4000K	28
BLC 2X4 5000LM 40K	191848536599	2x4 Center Basket Troffer, Square, Smooth Diffuser	4999	43W	120-277	4000K	28

Accessories: Order as separate catalog number.			
DGA24	Drywall grid adapter for 2x4 recessed fixture		
DGA22	Drywall grid adapter for 2x2 recessed fixture		
2X4 SMKSHP PAF	2X4 Surface Mount Troffer Kit		
2X2 SMKSHP PAF	2X2 Surface Mount Troffer Kit		
PS1050	LED emergency battery pack, 10W 50VDC (Noncompliant with CA T20)		
PS1055LCP	LED emergency battery pack, 10W Constant Power, Self-Diagnostic, Certified in CA Title 20 MAEDBS		
ELA PSRME IC	Remote enclosure for battery for insulated ceiling		
RK1BDP J40	Disconnect Plug (BDP) package of 40		
RK1BDP J10	Disconnect Plug (BDP) Package of 10		









# Specifications

### INTENDED USE:

The BLC troffer delivers soft, glare-free, ambient lighting in a popular center-basket design. The slim profile of the luminaire, coupled with energy-saving LED technology make the BLC an ideal choice for renovation or new construction. The BLC troffer offers a high-quality, cost-effective LED lighting solution for schools, offices, retail, healthcare facilities and other commercial spaces.

#### **CONSTRUCTION:**

The reflector is finished with a highly reflective paint for improved aesthetics and increased light diffusion. End plates contain easy-to-position integral T-bar clips for securely attaching the luminaire to the T-grid. For additional T-grid security, optional screw on T-bar clips are available. Diffusers are extruded from impact modified acrylic for increased durability. LED boards and drivers are accessible from the plenum.

#### **OPTICS:**

Volumetric illumination is achieved by creating an optimal mix of light to walls, partitions and vertical and horizontal work surfaces – rendering the interior space, objects and occupants in a more balanced, complimentary luminous environment. High performance extruded acrylic diffusers conceal LEDs and efficiently deliver light in a volumetric distribution.

#### **ELECTRICAL:**

Long-life LEDs, coupled with high-efficiency drivers, provide superior quantity and quality of illumination for extended service life. 80% LED lumen maintenance at 60,000 hours (L80/60,000). 0-10 volt dimming driver. Dims to 10%.

#### **INSTALLATION:**

With a depth of only 2-3/8", the BLC makes for an easy installation, especially in restrictive plenum applications. The BLC fits into standard 15/16" and narrow 9/16" T-grid ceiling systems. Suitable for damp location.

For recessed mounting in hard ceiling applications, Drywall Grid Adapters (DGA) are available as an accessory. See Accessories section.

#### LISTINGS:

CSA Certified to meet U.S. and Canadian standards. IC rated.

DesignLights Consortium<sup>®</sup> (DLC) qualified product. Not all versions of this product may be DLC qualified. Please check the DLC Qualified Products List at <u>www.designlights.org/QPL</u> to confirm which versions are qualified.

#### WARRANTY:


5-year limited warranty. This is the only warranty provided and no other statements in this specification sheet create any warranty of any kind. All other express and implied warranties are disclaimed. Complete warranty terms located at:

www.acuitybrands.com/support/customer-support/terms-and-conditions

**Note**: Actual performance may differ as a result of end-user environment and application. All values are design or typical values, measured under laboratory conditions at 25 °C. Specifications subject to change without notice.

# **Dimensions**

2X4 Length: 47-3/4 (121.2) 2X2 Length: 23-3/4 (60.3) Width: 23-3/4 (60.3) Depth: 2-3/8 (6.0)



All dimensions are inches (centimeters) unless otherwise indicated.