

Eaton BQ220250

Catalog Number: BQ220250

Eaton BR thermal magnetic circuit breaker, Type BQ 1-Inch CTL plug-on circuit breaker, Includes rejection tab feature, (1) Two-Pole 20 A, (1) Two-Pole 50 A, 10 kAIC, Four-pole, 120/240V, BQ, Independent, #14-4 AWG Cu/Al, Q28, BQ, Type BR Loadcenters

General specifications



Product Name	Catalog Number
Eaton BR thermal magnetic circuit breaker	BQ220250

UPC
786676370905

Product Length/Depth	Product Height
2 in	2.6 in

Product Width	Product Weight
3.1 in	0.75 lb

Compliances	Certifications
Federal Specifications Classification W-C375	UL 489

Catalog Notes

All Type BD Duplex and BQ Quadplex circuit breakers carry listing for HACR applications. All 15 and 20 ampere single poles are switch duty rated.

defaultTaxonomyAttributeLabel

Type

Type BQ 1-Inch CTL plug-on circuit breaker

Special features

Includes rejection tab feature

Amperage Rating

(1) Two-Pole 20A, (1) Two-Pole 50A

Voltage rating

120/240 V

Trip Type

Independent

Circuit breaker type

BQ

Used with

Type BR Loadcenters

Mounting Method

Plug-on

Interrupt rating

10 kAIC

Main circuit breaker

BQ

Wire size

#14-4 AWG Cu/Al

Number of poles

Four-pole

Quantity

28

Resources

Brochures

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Specifications and datasheets

Eaton Specification Sheet - BQ220250



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)