

# Eaton BQC2302120

Catalog Number: BQC2302120

Eaton BR thermal magnetic circuit breaker, Type BQC 1-Inch CTL plug-on circuit breaker, Includes rejection tab feature, (2) Single-Pole 20 A, (1) Two-Pole 30 A, 10 kAIC, Four-pole, 120/240V, BQC, Common breaker trip, #14-4 AWG Cu/Al, BQC

## General specifications



### Product Name

Eaton BR thermal magnetic circuit breaker

### Catalog Number

BQC2302120

### UPC

786676371780

### Product Length/Depth

3 in

### Product Height

3 in

### Product Width

2 in

### Product Weight

0.9 lb

### Compliances

Federal Specifications Classification W-C375

### Certifications

UL 489

### Catalog Notes

All Type BD Duplex and BQ Quadplex circuit breakers carry listing for HACR applications. All 15 and 20 ampere single poles are switch duty rated.

## defaultTaxonomyAttributeLabel

### Type

Type BQC 1-Inch CTL plug-on circuit breaker

### Special features

Includes rejection tab feature

### Amperage Rating

(2) Single-Pole 20A, (1) Two-Pole 30A

### Voltage rating

120/240 V

### Trip Type

Common breaker trip

### Circuit breaker type

BQ

### Used with

Type BR Loadcenters

### Mounting Method

Plug-on

### Interrupt rating

10 kAIC

### Main circuit breaker

BQC

### Wire size

#14-4 AWG Cu/Al

### Number of poles

Four-pole

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Specifications and datasheets

[Eaton Specification Sheet - BQC2302120](#)