

Eaton BQC230230

Catalog Number: BQC230230

Eaton BR thermal magnetic circuit breaker, Type BQC 1-Inch CTL plug-on circuit breaker, Includes rejection tab feature, (2) Two-Pole 30 A, 10 kAIC, Four-pole, 120/240V, BQC, Common breaker trip, #14-4 AWG Cu/Al, BQC, Type BR Loadcenters

General specifications



Product Name

Eaton BR thermal magnetic circuit breaker

Catalog Number

BQC230230

UPC

786676371896

Product Length/Depth

3 in

Product Height

3 in

Product Width

2 in

Product Weight

0.9 lb

Compliances

Federal Specifications Classification W-C375

Certifications

UL 489

Catalog Notes

All Type BD Duplex and BQ Quadplex circuit breakers carry listing for HACR applications. All 15 and 20 ampere single poles are switch duty rated.

defaultTaxonomyAttributeLabel

Type

Type BQC 1-Inch CTL plug-on circuit breaker

Special features

Includes rejection tab feature

Amperage Rating

(2) Two-Pole 30A

Voltage rating

120/240 V

Trip Type

Common breaker trip

Circuit breaker type

BQ

Used with

Type BR Loadcenters

Mounting Method

Plug-on

Interrupt rating

10 kAIC

Main circuit breaker

BQC

Wire size

#14-4 AWG Cu/Al

Number of poles

Four-pole

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - BQC230230](#)