

# Eaton BQC240240

Catalog Number: BQC240240

Eaton BR thermal magnetic circuit breaker, Type BQC 1-Inch CTL plug-on circuit breaker, Includes rejection tab feature, (2) Two-Pole 40 A, 10 kAIC, Four-pole, 120/240V, BQC, Common breaker trip, #14-4 AWG Cu/Al, BQC, Type BR Loadcenters

## General specifications



Product Name	Catalog Number
Eaton BR thermal magnetic circuit breaker	BQC240240
	UPC
	786676371926

Product Length/Depth	Product Height
3 in	3 in

Product Width	Product Weight
2 in	0.8 lb

Compliances	Certifications
Federal Specifications Classification W-C375	UL 489

### Catalog Notes

All Type BD Duplex and BQ Quadplex circuit breakers carry listing for HACR applications. All 15 and 20 ampere single poles are switch duty rated.

## defaultTaxonomyAttributeLabel

### Type

Type BQC 1-Inch CTL plug-on circuit breaker

### Special features

Includes rejection tab feature

### Amperage Rating

(2) Two-Pole 40A

### Voltage rating

120/240 V

### Trip Type

Common breaker trip

### Circuit breaker type

BQ

### Used with

Type BR Loadcenters

### Mounting Method

Plug-on

### Interrupt rating

10 kAIC

### Main circuit breaker

BQC

### Wire size

#14-4 AWG Cu/Al

### Number of poles

Four-pole

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Specifications and datasheets

[Eaton Specification Sheet - BQC240240](#)