

Eaton BQC240250

Catalog Number: BQC240250

Eaton BR thermal magnetic circuit breaker, Type BQC 1-Inch CTL plug-on circuit breaker, Includes rejection tab feature, (1) Two-Pole 40 A, (1) Two-Pole 50 A, 10 kAIC, Four-pole, 120/240V, BQC, Common breaker trip, #14-4 AWG Cu/Al, BQC



General specifications

Product Name	Catalog Number
Eaton BR thermal magnetic circuit breaker	BQC240250
	UPC
	786676371933

Product Length/Depth	Product Height
3 in	2.6 in

Product Width	Product Weight
2 in	0.8 lb

Compliances	Certifications
Federal Specifications Classification W-C375	UL 489

Catalog Notes

All Type BD Duplex and BQ Quadplex circuit breakers carry listing for HACR applications. All 15 and 20 ampere single poles are switch duty rated.

defaultTaxonomyAttributeLabel

Type

Type BQC 1-Inch CTL plug-on circuit breaker

Special features

Includes rejection tab feature

Amperage Rating

(1) Two-Pole 40A, (1) Two-Pole 50A

Voltage rating

120/240 V

Trip Type

Common breaker trip

Circuit breaker type

BQ

Used with

Type BR Loadcenters

Mounting Method

Plug-on

Interrupt rating

10 kAIC

Main circuit breaker

BQC

Wire size

#14-4 AWG Cu/Al

Number of poles

Four-pole

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - BQC240250](#)