

# Eaton BQC2502120

Catalog Number: BQC2502120

Eaton BR thermal magnetic circuit breaker, Type BQC 1-Inch CTL plug-on circuit breaker, Includes rejection tab feature, (2) Four-Pole 20 A, (1) Two-Pole 50 A, 10 kAIC, Four-pole, 120/240V, BQC, Common breaker trip, #14-4 AWG Cu/Al, BQC



## General specifications

Product Name	Catalog Number
Eaton BR thermal magnetic circuit breaker	BQC2502120
	UPC
	786676371827

Product Length/Depth	Product Height
3 in	3 in

Product Width	Product Weight
2 in	0.9 lb

Compliances	Certifications
Federal Specifications Classification W-C375	UL 489

### Catalog Notes

All Type BD Duplex and BQ Quadplex circuit breakers carry listing for HACR applications. All 15 and 20 ampere single poles are switch duty rated.

## defaultTaxonomyAttributeLabel

### Type

Type BQC 1-Inch CTL plug-on circuit breaker

### Special features

Includes rejection tab feature

### Amperage Rating

(2) Four-Pole 20A, (1) Two-Pole 50A

### Voltage rating

120/240 V

### Trip Type

Common breaker trip

### Circuit breaker type

BQ

### Used with

Type BR Loadcenters

### Mounting Method

Plug-on

### Interrupt rating

10 kAIC

### Main circuit breaker

BQC

### Wire size

#14-4 AWG Cu/Al

### Number of poles

Four-pole

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Specifications and datasheets

[Eaton Specification Sheet - BQC2502120](#)