

## Eaton BR thermal magnetic circuit breaker

BR115

UPC:786676362054

### Dimensions:

- **Height:** 3 IN
- **Length:** 3 IN
- **Width:** 1 IN

**Weight:** .3 LB

**Warranties:** No Data

### Specifications:

- **Type:** Type BR 1-Inch plug-on circuit breaker
- **Amperage Rating:** 15A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 120/240 V
- **Main Circuit Breaker:** BR
- **Wire Size:** #14-4 AWG Cu/Al
- **Used With:** Type BR Loadcenters

### Supporting documents:

- [Loadcenters and Circuit Breakers](#)
- [Eaton's Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - BR115](#)

### Certifications:

- UL 489

### Product compliance:

- Federal Specifications Classification W-C375

