

Eaton BR thermal magnetic circuit breaker

BR120

UPC:786676362108

Dimensions:

- **Height:** 3 IN
- **Length:** 2.5 IN
- **Width:** 1 IN

Weight:.3 LB

Warranties:

- Limited lifetime residential, 1 year commercial

Specifications:

- **Type:** Type BR 1-Inch plug-on circuit breaker
- **Amperage Rating:** 20A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 120/240 V
- **Main Circuit Breaker:** BR
- **Wire Size:** #14-4 AWG Cu/Al
- **Quantity:** Q1
- **Used With:** Type BR loadcenters

Supporting documents:

- [Retail Catalog](#)
- [Loadcenters and Circuit Breakers](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Type BR, BD, BQ, BQC,BRH, GFCB, GFCBH, 10-70Amp 1-Pole - Curve](#)
- [Eaton Specification Sheet - BR120](#)

Certifications:

- UL 489

Product compliance:

- Federal Specifications Classification W-C375

