Eaton BR120ST

Catalog Number: BR120ST

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 20 A, 10 kAIC, Single-pole, 120/240V, BR, #14-4 AWG Cu/Al,Q1,BR,Type BR loadcenters,Shunt trip included



General specifications

Product Name Eaton BR thermal magnetic circuit breaker Product Length/Depth 2.5 in **Product Width** 1 in

Warranty Limited lifetime residential, 1 year commercial

Certifications

UL 489

BR120ST
UPC 786676000161
Product Height 2 in
Product Weight 0.3 lb
Compliances

Federal Specifications Classification W-C375



defaultTaxonomyAttributeLabel

Туре

Type BR 1-Inch plug-on circuit breaker

Special features

Shunt trip

Amperage Rating

20 A

Voltage rating

120/240 V

Circuit breaker type

BR

Shunt trip

Included

Used with

Type BR Loadcenters

Mounting Method

Plug-on

Interrupt rating

10 kAIC

Main circuit breaker

BR

Wire size

#14-4 AWG Cu/Al

Number of poles

Single-pole

Quantity

1

Resources

Brochures

Loadcenters and Circuit Breakers

Catalogs Eaton's Volume 1—Residential and Light Commercial

Specifications and datasheets

Eaton Specification Sheet - BR120ST



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2024 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia