Eaton BR1224L125

Catalog Number: BR1224L125

Eaton Eaton BR main lug loadcenter ,No feed-thru lugs,Main lug,200 A,D1R,Aluminum,Cover included,NEMA 3R,Metallic,25 kAIC,BWH,NEMA 3R,40 Circuits,Twenty-four pole,30 Spaces,Three-wire

General specifications

Product Name Eaton BR main lug loadcenter

UPC

786676446556

Product Height 16.75 in

Product Weight 15.6 lb

Certifications UL 67

UL 50

Catalog Number BR1224L125

Product Length/Depth 3.88 in

Product Width 14.31 in

Warranty 10 year

Catalog Notes

Suitable for use as service equipment when no more than 6 main disconnecting means are provided or when not used as lighting & appliance panelboard. Has notch for brhdk125 hold-down kit.



defaultTaxonomyAttributeLabel

Special features

No feed-thru lugs, includes BREQS125 hold-down screw

Туре

Main lug

Amperage Rating

125 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Mounting

Combination

Number of circuits

24

Number of spaces

12

Phase

Single-phase

Used with Type BR 1-inch breakers

Voltage rating

120/240V

Wire size #6-2/0 AWG Cu/Al

Box size

B1

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Resources

Brochures Loadcenters and Circuit Breakers Type BR Arc Fault Circuit Breakers and Loadcenters Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings Dimensional Drawing - BR 1 LOADCENTER, MAIN LUG ONLY, INDOOR NEMA 1, 120/240 VAC, 1 PHASE

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Specifications and datasheets

Eaton Specification Sheet - BR1224L125

3



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Righ Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2024 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia