

Eaton BR1224L125G

Catalog Number: BR1224L125G

Eaton BR main lug loadcenter ,No feed-thru lugs, includes BREQS125 hold-down screw,Main lug,125 A,B2R,Aluminum,Cover included,NEMA 3R,Metallic,10 kAIC,BR,NEMA 3R,24 Circuits,Twenty-four pole,16 Spaces,Three-wire,Single-phase

General specifications



Product Name	Catalog Number
Eaton BR main lug loadcenter	BR1224L125G
UPC	Product Length/Depth
786676446600	3.88 in
Product Height	Product Width
16.75 in	14.31 in
Product Weight	Warranty
15.8 lb	10 year
Certifications	Catalog Notes
UL 50 UL 67	Suitable for use as service equipment when no more than 6 main disconnecting means are provided or when not used as lighting & appliance panelboard. Has notch for brhdk125 hold-down kit.

defaultTaxonomyAttributeLabel

Special features

Ground bar, includes BREQS125 hold-down screw

Type

Main lug

Amperage Rating

125 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Mounting

Combination

Number of circuits

24

Number of spaces

12

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240V

Wire size

#6-2/0 AWG Cu/Al

Box size

B1

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

[Type BR Arc Fault Circuit Breakers and Loadcenters](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Drawings

[Dimensional Drawing - BR 1 LOADCENTER, MAIN LUG ONLY, INDOOR NEMA 1, 120/240 VAC, 1 PHASE](#)

Installation instructions

[Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)

Specifications and datasheets

[Eaton Specification Sheet - BR1224L125G](#)

Number of wires

3



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia