

# Eaton BR160

Catalog Number: BR160

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 60 A, 10 kAIC, Single-pole, 120/240V, BR, #4-1/0 AWG Cu/Al, BR, Type BR Loadcenters



## General specifications

|  |                       |
|--|-----------------------|
| <b>Product Name</b>                          | <b>Catalog Number</b> |
| Eaton BR thermal magnetic circuit breaker    | BR160                 |
|  | UPC                   |
|  | 786676362351          |
| <b>Product Length/Depth</b>                  | <b>Product Height</b> |
| 3 in   | 3 in                  |
| <b>Product Width</b>                         | <b>Product Weight</b> |
| 1 in   | 0.3 lb                |
| <b>Compliances</b>                           | <b>Certifications</b> |
| Federal Specifications Classification W-C375 | UL 489                |

## Type

Type BR 1-Inch plug-on circuit breaker

## Amperage Rating

60 A

## Voltage rating

120/240 V

## Circuit breaker type

BR

## Used with

Type BR Loadcenters

## Mounting Method

Plug-on

## Interrupt rating

10 kAIC

## Main circuit breaker

BR

## Wire size

#4-1/0 AWG Cu/Al

## Number of poles

Single-pole

## Brochures

[Loadcenters and Circuit Breakers](#)

## Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

## Specifications and datasheets

[Eaton Specification Sheet - BR160](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)