

Specifications



Eaton BR1624L125R

Eaton Eaton BR main lug loadcenter, No feed-thru lugs, includes BREQS125 hold-down screw, 125 A, B2R, Al, NEMA 3R, Metallic, 10 kAIC, 24 Circuits, Twenty-four pole, 16 Spaces, Three-wire, 1ph, Type BR 1-inch breakers, 120/240V, #6-2/0 AWG Cu/Al

General specifications

PRODUCT NAME	Eaton BR main lug loadcenter
CATALOG NUMBER	BR1624L125R
UPC	786676446853
PRODUCT LENGTH/DEPTH	5.19 in
PRODUCT HEIGHT	18.75 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	15.5 lb
WARRANTY	10 year
CERTIFICATIONS	UL 50 UL 67
CATALOG NOTES	Has notch for brhdk125 hold-down kit.



Powering Business Worldwide

Product specifications

SPECIAL FEATURES	No feed-thru lugs, includes BREQS125 hold-down screw
TYPE	Main lug
AMPERAGE RATING	125 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	BR
NUMBER OF CIRCUITS	24
NUMBER OF SPACES	16
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240V
WIRE SIZE	#6-2/0 AWG Cu/Al
BOX SIZE	B2R
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NUMBER OF WIRES	3

Resources

CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BR1624L125R
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

