

# Eaton BR2024L125RG

Catalog Number: BR2024L125RG

Eaton BR main lug loadcenter, Ground bar, includes BREQS125 hold-down screw, 125 A, C1R, Aluminum, NEMA 3R, Metallic, 10 kAIC, NEMA 3R, 24 Circuits, Twenty-four pole, 20 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240V, #6-2/0 AWG Cu/Al



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main lug loadcenter	BR2024L125RG
<b>UPC</b>	<b>Product Length/Depth</b>
786685135267	5.19 in
<b>Product Height</b>	<b>Product Width</b>
21 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
15.8 lb	10 year
<b>Certifications</b>	<b>Catalog Notes</b>
UL 67 UL 50	Has notch for brhdk125 hold-down kit.

## defaultTaxonomyAttributeLabel

### Special features

Ground bar, includes BREQS125 hold-down screw

### Type

Main lug

### Amperage Rating

125 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR

### Number of circuits

24

### Number of spaces

20

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240V

### Wire size

#6-2/0 AWG Cu/Al

### Box size

C1R

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### Number of wires

3

## Resources

### Brochures

Loadcenters and Circuit Breakers

Type BR Arc Fault Circuit Breakers and Loadcenters

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - BR 1 LOADCENTER, MAIN LUG ONLY, OUTDOOR NEMA 3R, 120/240 VAC, 1 PHASE

### Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

### Specifications and datasheets

Eaton Specification Sheet - BR2024L125RG



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)