

# Eaton BR2030

Catalog Number: BR2030

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, c, 120V, BR, Common breaker trip, #14-4 AWG Cu/Al, Q28, BR, Type BR Loadcenters



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR thermal magnetic circuit breaker	BR2030
	UPC
	786676006606
<b>Product Length/Depth</b>	<b>Product Height</b>
3 in	3 in
<b>Product Width</b>	<b>Product Weight</b>
1 in	0.3 lb
<b>Warranty</b>	<b>Compliances</b>
Limited lifetime residential, 1 year commercial	Federal Specifications Classification W-C375
<b>Certifications</b>	
UL 489	

## defaultTaxonomyAttributeLabel

### Type

Type BR 1-Inch plug-on circuit breaker

### Amperage Rating

(1) 20A, (1) 30A

### Voltage rating

120 V

### Trip Type

Common breaker trip

### Circuit breaker type

BR

### Used with

Type BR Loadcenters

### Mounting Method

Plug-on

### Interrupt rating

10 kAIC

### Main circuit breaker

BR

### Wire size

#14-4 AWG Cu/Al

### Number of poles

Two-pole

### Quantity

28

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Specifications and datasheets

[Eaton Specification Sheet - BR2030](#)