

# Eaton BR2040B200R

Catalog Number: BR2040B200R

BR style 1-inch loadcenter, main circuit breaker, no feed-thru lugs, 200A, single-phase, 40-pole, 40 circuits, 20 spaces, 120/240V, #2/0-300 kcmil Cu/Al at 60°C or 75°C wire, NEMA 3R enclosure, d1r box size



## General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BR2040B200R
UPC	Product Length/Depth
786676445757	3.88 in
Product Height	Product Width
21 in	14.31 in
Product Weight	Warranty
35.13 lb	10 year
Certifications	
UL 50	
UL 67	

## defaultTaxonomyAttributeLabel

### Special features

No feed-thru lugs

### Type

Main circuit breaker

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BWH

### Number of circuits

40

### Number of spaces

20

### Phase

Single-phase

### Wire size

#2/0 AWG-300 kcmil Cu/Al

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

D1R

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Brochures

Loadcenters and Circuit Breakers

Type BR Arc Fault Circuit Breakers and Loadcenters

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - BR 1 LOADCENTER, CSR MAIN BREAKER, OUTDOOR NEMA 3R, 120/240 VAC, 1 PH

### Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

### Specifications and datasheets

Eaton Specification Sheet - BR2040B200R



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)