

# Eaton BR2040N200R

Catalog Number: BR2040N200R

Eaton BR convertible loadcenter, No feed-thru lugs, Convertible main, 200 A, D1r, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, BR, 40 Circuits, 20 Spaces, Three-wire, Single-phase, 120/240 V, Determined by circuit breaker installed



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR convertible loadcenter	BR2040N200R
<b>UPC</b>	<b>Product Length/Depth</b>
786676448703	3.88 in
<b>Product Height</b>	<b>Product Width</b>
21 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
40 lb	10 year
<b>Certifications</b>	<b>Catalog Notes</b>
UL 50 UL 67	The maximum rating of the panel is the main breaker rating when used as service entrance equipment.

## defaultTaxonomyAttributeLabel

### Special features

No feed-thru lugs

### Type

Convertible main

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR

### Number of circuits

40

### Number of spaces

20

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Wire size

Determined by circuit breaker installed

### Box size

D1R

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Brochures

Loadcenters and Circuit Breakers

Type BR Arc Fault Circuit Breakers and Loadcenters

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - BR 1 LOADCENTER, CSR CONVERTIBLE, OUTDOOR NEMA 3R, 120/240 VAC, 1 PHASE

### Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

### Specifications and datasheets

Eaton Specification Sheet - BR2040N200R



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)