

# Eaton BR2040N200RG

Catalog Number: BR2040N200RG

Eaton BR convertible loadcenter, Ground bar, Convertible main, 200 A, D1r, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, 40 Circuits, 20 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V, Determined by circuit breaker installed



## General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BR2040N200RG
UPC	Product Length/Depth
782116893911	5.19 in
Product Height	Product Width
21 in	14.31 in
Product Weight	Warranty
40 lb	10 year

## Certifications

UL 50  
UL 67

## defaultTaxonomyAttributeLabel

### Special features

Ground bar

### Type

Convertible main

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR

### Number of circuits

40

### Number of spaces

20

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Wire size

Determined by circuit breaker installed

### Box size

D1R

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Brochures

Loadcenters and Circuit Breakers

Type BR Arc Fault Circuit Breakers and Loadcenters

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - BR 1 LOADCENTER, CSR CONVERTIBLE, OUTDOOR NEMA 3R, 120/240 VAC, 1 PHASE

### Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

### Specifications and datasheets

Eaton Specification Sheet - BR2040N200RG



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)