

# Specifications

## Eaton BR20RD

Eaton commercial specification grade duplex receptacle, #14-10 AWG, 20A, Commercial, Flush, 125V, Back and side, Red, Brass, High-impact nylon, PVC, 5-20R, Duplex, Screw, PVC, Core pack

### General specifications

<b>PRODUCT NAME</b>	Eaton commercial specification grade duplex receptacle
<b>CATALOG NUMBER</b>	BR20RD
<b>UPC</b>	032664654312
<b>PRODUCT LENGTH/DEPTH</b>	1.3 in
<b>PRODUCT HEIGHT</b>	4.2 in
<b>PRODUCT WIDTH</b>	0.88 in
<b>PRODUCT WEIGHT</b>	0.21 lb
<b>CERTIFICATIONS</b>	UL NOM Federal Specification Classification 6233 01
<b>PRODUCT TYPE</b>	Commercial specification grade



Powering Business Worldwide

## Product specifications

<b>DEVICE TYPE</b>	Receptacle
<b>TYPE</b>	Duplex receptacle
<b>AMPERAGE RATING</b>	20A
<b>VOLTAGE RATING</b>	125V
<b>CONTACT MATERIAL</b>	Brass
<b>FEATURES</b>	Auto-grounding
<b>APPLICATION</b>	Commercial
<b>DEVICE GRADE</b>	Commercial
<b>WIRING METHOD</b>	Back and side
<b>NUMBER OF WIRES</b>	3
<b>MOUNTING METHOD</b>	Flush
<b>NUMBER OF POLES</b>	Two-pole
<b>STYLE TYPE</b>	Standard
<b>MATERIAL</b>	PVC
<b>PACKAGING TYPE</b>	Core pack
<b>COLOR</b>	Red
<b>CONNECTION TYPE</b>	Screw
<b>ALLOWABLE WIRE SIZE</b>	Side or Back Wiring :#10-14 Copper or Copper Clad Aluminum
<b>NEMA CONFIGURATION</b>	5-20R
<b>TORQUE RATING</b>	14 lbf-inch
<b>DESIGN TYPE</b>	Straight blade
<b>FACE/BODY MATERIAL</b>	High-impact nylon PVC
<b>RECEPTACLE TYPE</b>	Duplex

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

## Resources

MULTIMEDIA	<a href="#">Residential straight blade receptacles</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - BR20RD</a>
	<a href="#">Commercial grade straight blade duplex receptacles spec sheet</a>



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

