

Eaton BR thermal magnetic circuit breaker

BR215

UPC:786676362801

Dimensions:

- **Height:** 2.5 IN
- **Length:** 1.9 IN
- **Width:** 2.9 IN

Weight:.5 LB

Warranties: No Data

Specifications:

- **Type:** Type BR 1-Inch plug-on circuit breaker
- **Amperage Rating:** 15A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Two-pole
- **Voltage Rating:** 120/240 V
- **Main Circuit Breaker:** BR
- **Trip Type:** Common breaker trip
- **Wire Size:** #14-4 AWG Cu/Al
- **Quantity:** Q28
- **Used With:** Type BR Loadcenters

Supporting documents:

- [Loadcenters and Circuit Breakers](#)
- [Eaton's Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - BR215](#)

Certifications:

- UL 489

Product compliance:

- Federal Specifications Classification W-C375

