

Eaton BR2424L125G

Catalog Number: BR2424L125G

Eaton Eaton BR main lug loadcenter, Ground bar, includes BREQS125 hold-down screw, 125 A, C2, Aluminum, NEMA 1, Metallic, 10 kAIC, Combination, NEMA 1, 24 Circuits, Twenty-four pole, 24 Spaces, Three-wire, Single-phase, 120/240V, #6-2/0 AWG Cu/Al



General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BR2424L125G
UPC	Product Length/Depth
786676001199	3.88 in
Product Height	Product Width
23 in	14.31 in
Product Weight	Warranty
16 lb	10 year
Certifications	Catalog Notes
UL 50 UL 67	Ground bar gbk1220 is installed. Has notch for brhdk125 hold-down kit.

defaultTaxonomyAttributeLabel

Special features

Ground bar, includes BREQS125 hold-down screw

Type

Main lug

Amperage Rating

125 A

Bus material

Aluminum

Cover

Cover included

Mounting

Combination

Number of circuits

24

Number of spaces

24

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240V

Wire size

#6-2/0 AWG Cu/Al

Box size

C2

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

3

Resources

Brochures

Loadcenters and Circuit Breakers

Type BR Arc Fault Circuit Breakers and Loadcenters

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - BR 1 LOADCENTER, MAIN LUG ONLY, INDOOR
NEMA 1, 120/240 VAC, 1 PHASE

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Specifications and datasheets

Eaton Specification Sheet - BR2424L125G



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)