Eaton BR24L125RP

Catalog Number: BR24L125RP

Eaton BR main lug loadcenter, Current design, Rainproof panels are furnished with hub closure plates, Main lug, 125 A,6R, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, 4 Circuits, 2 Spaces, Three-wire, Single-phase

General specifications



Product Name

Eaton BR main lug loadcenter

UPC

786676001502

Product Height

4.7 in

Product Weight

6.45 lb

Certifications

UL 50 UL 67 Catalog Number

BR24L125RP

Product Length/Depth

13 in

Product Width

7.2 in

Warranty

10 year

Catalog Notes

Ground bar kit priced separately.

Suitable for use as service equipment

when no more than 2 service

disconnecting mains are provided or when not used as lighting & appliance

panelboard



defaultTaxonomyAttributeLabel

Special features Current design

Type

Main lug

Amperage Rating

125 A

Bus material Aluminum

Cover

Cover included

Number of circuits

4

Number Of Poles

Four-pole

Number of spaces

2

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Wire size

#14-1/0 AWG Cu/AI

Box size

6R

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

3

Resources

Brochures

Loadcenters and Circuit Breakers

Type BR Arc Fault Circuit Breakers and Loadcenters

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Specifications and datasheets

Eaton Specification Sheet - BR24L125RP



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia